

# WALL MOUNT HANDGUN LOCKERS



by Spacesaver®

## INSTALLATION INSTRUCTIONS

**SECTION I**  
LOCKER LAYOUTS

**SECTION II**  
LOCKER INSTALLATION

**SECTION III**  
LOCK OPTIONS



### CAUTION

Spacesaver Recommends:

1. That Safety Glasses be worn during any cutting and drilling operations and grinding.
2. That safety gear such as Hard Hats, Safety Shoes, etc. be worn when required.

  
**STOREMORESTORE**  
Efficient **Productive** Storage Products

[www.StoreMoreStore.com](http://www.StoreMoreStore.com)

Phone 1-855-786-7667

# CONTENTS

---

<b>PAGE #</b>	<b>SECTION I - WALL MOUNT LOCKER LAYOUTS</b>
---------------	--

---

3

---

	<b>SECTION II - LOCKER INSTALLATION</b>
--	---

---

4 Surface Mount

5 Flush Mount

---

	<b>SECTION III - LOCK OPTIONS</b>
--	-----------------------------------

---

6 Manual Purpose/Use

## TOOL REQUIREMENTS

Drill with drill bit set (Sizes of bit determined by hardware used)

DSM Master Key **ss# 550609.001**

Tape Measure

Phillips and Flat Head Screwdrivers


**NOTE: Fastening hardware is not provided as wall materials vary.**

# WALL MOUNT LOCKER LAYOUTS

## FLUSH AND SURFACE MOUNT

### WALL MOUNT HAND GUN LOCKERS MODELS HGS & HGF


MODEL NUMBER	TYPE OF MOUNTING	NUMBER OF OPENINGS	ACTUAL SIZE OF CABINET				SIZE OF WALL OPENING		
			WIDTH	HEIGHT	DEPTH	WEIGHT	WIDTH	HEIGHT	DEPTH
HGS-02V	SURFACE	2	13"	14 1/8"	6 1/2"	17 lbs	NONE		
HGF-02V	FLUSH	2	13"	14 1/8"	6 1/2"	20 lbs	13 1/2"	14 1/2"	6 1/2"
HGS-03V	SURFACE	3	13"	20 1/8"	6 1/2"	24 lbs	NONE		
HGF-03V	FLUSH	3	13"	20 1/8"	6 1/2"	27 lbs	13 1/2"	20 1/2"	6 1/2"
HGS-04V	SURFACE	4	13"	26 1/8"	6 1/2"	28 lbs	NONE		
HGF-04V	FLUSH	4	13"	26 1/8"	6 1/2"	31 lbs	13 1/2"	26 1/2"	6 1/2"
HGS-04	SURFACE	4	25"	14 1/8"	6 1/2"	29 lbs	NONE		
HGF-04	FLUSH	4	25"	14 1/8"	6 1/2"	32 lbs	25 1/2"	14 1/2"	6 1/2"
HGS-06	SURFACE	6	25"	20 1/8"	6 1/2"	49 lbs	NONE		
HGF-06	FLUSH	6	25"	20 1/8"	6 1/2"	53 lbs	25 1/2"	20 1/2"	6 1/2"
HGS-08	SURFACE	8	25"	26 1/8"	6 1/2"	55 lbs	NONE		
HGF-08	FLUSH	8	25"	26 1/8"	6 1/2"	59 lbs	25 1/2"	26 1/2"	6 1/2"
HGS-10	SURFACE	10	25"	32 1/8"	6 1/2"	78 lbs	NONE		
HGF-10	FLUSH	10	25"	32 1/8"	6 1/2"	82 lbs	25 1/2"	32 1/2"	6 1/2"




HGS-02V




HGS-03V




HGS-04V




HGS-04




HGS-06




HGS-08



HGS-10




SURFACE MOUNT  
HGS



FLUSH MOUNT  
HGF

### FLUSH MOUNT



## SURFACE MOUNT

### Step 1

Mark out where on the wall you want to put the locker. Make sure that the locker will sit flush up against the wall, free from obstructions.



### Step 2

Open the top and bottom door(s) of the locker. This will reveal the top and bottom mounting points.



Each locker has (4) 9/32" mounting holes located in both the top and bottom compartments.



### Step 3

Hold the locker up to the wall and mark out the 4 mounting points. Drill (4) mounting holes (hole dia. is 9/32") for anchoring the locker. Mount locker using the appropriate hardware.

**NOTE: Fastening hardware is not provided as wall materials vary.**




## FLUSH MOUNT

Flush mount wall mount lockers have a 1 1/2" frame running around the front of the locker. This trim is 1/2" thick, and adds an additional 3" to both the height and width of the front of the locker.



Place the locker in the wall cutout. Mark out the 4 mounting points. Drill (4) mounting holes (hole dia. is 9/32") for anchoring the locker. Mount locker using the appropriate hardware.


**NOTE: Fastening hardware is not provided as wall materials vary.**



## LOCK OPTIONS

### DSM Tube Lock- 7/8" SS# 550531.001


This is the standard lock used in the wall mount gun lockers (flush and surface mount). For service and installation information see OP# 0728



### Medeco Camlock- 7/8"

Medeco cam locks are used where key control is a concern. Locks and replacement keys must be ordered by the customer, directly from the manufacture. The installation for these locks is the same as the standard DSM tube lock. See OP-0728

For more information, visit:  
<http://www.medeco.com/>



### Digilock

Digilock keypad locks are an optional lock for the wall mount handgun locker. They allow multiple users to access lockers without the need for keys. For more information about servicing lockers with Digilock, see OP #0731.

